



Donaldson  
FILTRATION SOLUTIONS

# Process Filtration From Pure to Sterile

P-KG

## MAIN FEATURES & BENEFITS:

- Highly durable all-Polypropylene design
- Built-in ventilation valve
- Resistant towards hydraulic shocks
- Up to 76 l/min



## INDUSTRIES:



- Photo Industry



- Food and Beverage Industry



- Chemical Industry



- Electronics Industry



- Engineering



- Environmental

Donaldson Filtration Deutschland GmbH  
Büssingstr. 1  
42781 Haan (Germany)  
Phone: +49 (0) 2129 569 0  
Fax: +49 (0) 2129 569 100  
E-mail: IFS-de@donaldson.com  
Web: [www.donaldson.com](http://www.donaldson.com)

Donaldson®  
Ultrafilter

## PRODUCT DESCRIPTION

The Donaldson plastic housing P-KG is a particularly economic solution for the filtration of liquid media. The filter distinguishes itself by a robust construction that is unsusceptible to shock. An air-release valve on the inlet is standard.

Donaldson offers 2 versions. The version with brass screw-in thread and EPDM sealings at housing-connections find its application e.g. in the water-filtration. The ventilation is realised with a brass plug.

The version with connection-threads made of PP-plastic and sealings made of Viton, has been conceived for the filtration in critical areas. In this version, a polypropylene ventilation-valve is installed.

The dimensions of the respective types are identical.

## TECHNICAL DATA

### Technical Data

<b>Materials Filter Housing:</b>	break resistant polypropylene
<b>Materials Housing Gasket:</b>	EPDM O-ring (connections made of brass) Viton O-ring (connections made of plastic)
<b>Maximum Operating Pressure:</b>	8 bar at 50°C
<b>Adapters:</b>	The P-KG housings can only be used with filter elements with DOE (double open end) connections.

Type P-KG	Maximum Flow rate*	Element Length	Dimensions			Weight
			Height	Locating Distance	Connection	
0072	38 l/min	254 mm	294 mm	122 mm	G ¾	0,7 kg
0144	76 l/min	508 mm	570 mm	122 mm	G1	1,2 kg

\* no element inside / housing only

Technical alterations reserved 04/2009

- For information on test equipment or test services, please contact your Donaldson Sales Engineer and visit our website at [www.donaldson.com!](http://www.donaldson.com!)

